




2 RIGHT VIEW




1 FRONT VIEW




6 BOTTOM VIEW




5 TOP VIEW



3 LEFT VIEW



4 BACK VIEW



Applicable Model

R28

Drawing Title

Wall Mounting Box

Drawing Unit

mm

Drawing Scale

Not to scale

DRAFT
SUBJECT TO
CHANGE

Last Revised


Apr 25,2020

Drawing Version


V1.0

Page


2 of 6




5 TOP VIEW




2 RIGHT VIEW




1 FRONT VIEW




3 LEFT VIEW



4 BACK VIEW



6 BOTTOM VIEW





1 INTERCOM PANEL FRONT VIEW

1100mm TO BOTTOM OF PANEL

1231mm MAX TO TOP OF USABLE PARTS



ADA Compliance Requirement



2 FRONT VIEW:WALL MOUNTING BOX PLACEMENT

1101mm TO BOTTOM OF BOX

1260mm TO SCREW HOLE CENTER OF BOX



3 SIDE VIEW:INTERCOM ON WALL

Applicable Model

R28

Drawing Title

Flush Mounting Bracket

Drawing Unit

mm

Drawing Scale

Not to scale

DRAFT
SUBJECT TO
CHANGE

Last Revised


Apr 25,2020

Drawing Version


V1.0

Page


4 of 6




5 TOP VIEW




2 RIGHT VIEW




1 FRONT VIEW




3 LEFT VIEW



4 BACK VIEW



6 BOTTOM VIEW



2 RIGHT VIEW

1 FRONT VIEW


3 LEFT VIEW

4 BACK VIEW

6 BOTTOM VIEW

5 TOP VIEW

Applicable Model R28
Drawing Title Flush Mounting Box
Drawing Unit mm
Drawing Scale Not to scale
DRAFT SUBJECT TO CHANGE
Last Revised Apr 25,2020
Drawing Version V1.0
Page 4 of 6





1 INTERCOM PANEL FRONT VIEW

1100mm TO BOTTOM OF PANEL

1231mm MAX TO TOP OF USABLE TPARTS



ADA Compliance Requirement



2 FRONT VIEW: FLUSHING MOUNTING BOX PLACEMENT

1105mm TO BOTTOM OF BOX

1240mm TO SCREW HOLE CENTER OF BOX



3 SIDE VIEW:INTERCOM IN WALL